


ROLINE USB Wall Charger Euro Plug, 2 Ports, 2x C (PD), 100W, GaN

Product No.	19.11.1053	
Manufacturer	ROLINE	
Manufacturer No.	19.11.1053	



2-port USB charger, 2x Type C with maximum 100W for the power supply (smartphones, tablets) of several devices simultaneously

- For charging of mobile devices (tablets / smartphones)
- Quick Charge 3.0 / Type C (PD) supported
- Multi-Protection: Over Current / Short Circuit / Over Voltage Protection
- Compact Design
- Power IQ technology - identifies what kind of device is plugged in and delivers the proper voltage/amperage
- Input: 100 - 240 V AC, 50 - 60 Hz
- Output Type C (PD): DC 5V / 3A, 9V / 3A, 12V / 3A / 15V / 3A / 20V / 5A (one port charging)
20V / 2.25 A (two port charging)
- Total output: max. 100W

Advantages of GaN technology

- GaN or gallium nitride - crystalline material with more advantageous properties compared to silicon
- Powerful, efficient power supply
- Enables more compact charger design
- Low heat generation
- Allows a higher density of electronic components

Technical specifications

Manufacturer	ROLINE
Product group	Voltage converter

Product type	USB charger
Colour	white
Input	100-240 VAC
Output	DC 5V / 3A, 9V / 3A, 12V / 3A / 15V / 3A / 20V / 5A (one port charging) 20V / 2.25 A (two port charging)
Output	100W
Dimensions (HxWxD)	66 x 32 x 104 mm
Input connector	Euro Plug
Output connector	2x Type C
Technical particularity	GaN Technology
Mains connection	Euro plug
Height	66 mm
Width	32 mm
Depth	104 mm
Weight	215 g