

Item no.: 19.11.1054

**ROLINE USB GaN Charger, 38W, USB-C(PD)+USB-A(QC)
white**



Features:

- 2-port charger supports total max. 38W output
- It can charge 2 devices simultaneously
- Equipped with advanced PD 3.0 & QC 3.0 fast charging technology
- Advanced GaN Technology makes the charger smaller and more efficient
- Input: AC 100 ~ 240V, 50/60Hz, 1A(Max.)
- Output: USB-C – DC 5V/3A, 9V/2.22A, 12V/1.67A (20W Max.)
- Output: USB-A – DC 3.6~6V/3A, 6~9V/2A, 9~12V/1.5A (18W Max.)
- Built-in safeguards protect your devices against over-heating, over-voltage, short-circuit
- ABS casing in white color
- Operating Temperature: 0°C to 40°C
- Storage Temperature: -20°C to 80°C
- Operating Humidity: 20%~80% RH (Non-condensing)
- Storage Humidity: 10%~90% RH (Non-condensing)