

PANEL MOUNT INDICATOR, NON-RELAMPABLE

LED TECHNOLOGY

MOUNTING HOLE, Ø 0.310"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
LED 6V SERIES				
WL-2191L1-6V	RED	5V-6V	20mA	100,000
WL-2191L5-6V	GREEN	5V-6V	20mA	100,000
WL-2191L7-6V	YELLOW	5V-6V	20mA	100,000
LED 12V SERIES				
WL-2191L1-12V	RED	12V-14V	20mA	100,000
WL-2191L5-12V	GREEN	12V-14V	20mA	100,000
WL-2191L7-12V	YELLOW	12V-14V	20mA	100,000
LED 24V SERIES				
WL-2191L1-24V	RED	24V-28V	20mA	100,000
WL-2191L5-24V	GREEN	24V-28V	20mA	100,000
WL-2191L7-24V	YELLOW	24V-28V	20mA	100,000

NOTES

1. Minimum panel thickness 0.030"
2. 6" leads with 1/2" strip are standard
3. Storage temperature
T_{STG}: -25°C - +80°C
4. Ambient temperature
T_A: -20°C - +60°C
5. Voltage tolerance
V_{OP}: ±10%
6. Body material
Nylon, white
7. Lens material
Polycarbonate
8. Bezel material
Chrome
9. Wire gauge
18 AWG
10. Wire strip
1/2"
11. Anode(+)
Red lead


CERTIFICATIONS

UL (E340667), RoHS



RoHS
COMPLIANT

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

