



## PRESSLASCHENBLINDNIETE (LEICHTBAU) FLACHRUNDKOPF

## TRIPLE CLAW BLIND RIVETS (LIGHT WEIGHT CONSTRUCTION) DOMED HEAD

## RIVETS TRIPLE (CONSTRUCTION LÉGÈRE) TÊTE PLATE



Aluminium AIMG 3 / 3,5 (5154)  
Aluminium AIMG 3 / 3,5 (5154)  
Aluminium AIMG 3 / 3,5 (5154)

Aluminium AIMG 5 (5056)  
Aluminium AIMG 5 (5056)  
Aluminium AIMG 5 (5056)

### Ø 4,0 mm

D1 = 4,0 + / - 0,10 mm  
D2 = 8,0 + / - 0,29 mm  
k = ≤ 1,7 mm  
d = 2,5 mm  
P = ≥ 27,0 mm  
L = + 0,99 / - 0,2 mm

4,2 mm (max. 4,4 mm)

	F-Max		CODE				
4,0 x 13,6 mm	17,6 mm	1,0 - 3,0 mm	70994 01360	500 N	800 N	500	5000
4,0 x 18,8 mm	22,8 mm	3,0 - 7,0 mm	70994 01808			500	5000
4,0 x 21,0 mm	25,0 mm	5,0 - 9,0 mm	70994 02105			500	5000

### Ø 4,8 mm

D1 = 4,8 + / - 0,10 mm  
D2 = 9,6 + / - 0,29 mm  
k = ≤ 2,0 mm  
d = 2,9 mm  
P = ≥ 27,0 mm  
L = + 0,99 / - 0,2 mm

5,0 mm (max. 5,2 mm)

	F-Max		CODE				
4,8 x 15,3 mm	19,8 mm	1,0 - 3,0 mm	70994 81530	800 N	1100 N	500	5000
4,8 x 20,5 mm	25,0 mm	3,0 - 9,0 mm	70994 82050			500	5000
4,8 x 24,5 mm	29,0 mm	5,0 - 12,0 mm	70994 82450			500	5000