

## TOLEDO CANDLE

ToLEDo CANDLE V6 470LM 840 E14 SL  
0027515



### Product features

- Compact and elegant design
- Suitable replacement for halogen, incandescent and compact fluorescent candle lamps
- Instant light at the flick of a switch
- Uniform light distribution
- Good colour rendering (CRI 80)
- Perfect for hotels, restaurants, lobbies, corridors, stairwells, reception areas
- Lower maintenance costs
- A+ energy rating



### PRODUCT OVERVIEW

Product name	ToLEDo CANDLE V6 470LM 840 E14 SL
Technology	LED
Watt (Rated) (W)	5
Cap/Base	E14
Fixture rating	Open
General application	Education, Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740659
Warranty	3 years
Luminous flux (lm)	470
Colour temperature (K)	4000
Light colour	Cool White
CRI (Ra)	80
Beam Angle (°)	180
Wattage (W)	5
Product Voltage (V)	230
Average life (Nominal) (h)	15000
Product EAN number	5410288275154

### DATA TABLE

#### General data

Product name	ToLEDo CANDLE V6 470LM 840 E14 SL
Technology	LED
Watt (Rated) (W)	5
Cap/Base	E14
Fixture rating	Open
General application	Education, Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4740659
Warranty	3 years

## TOLEDO CANDLE

ToLEDo CANDLE V6 470LM 840 E14 SL  
0027515

### Optical data

Luminous flux (lm)	470
Luminous flux (Rated) (lm)	470
Colour temperature (K)	4000
Light colour	Cool White
CRI (Ra)	80
Beam Angle (°)	180
Lumen maintenance at end of nominal life (%)	70

### Electrical data

Wattage (W)	5
Equivalent watt (W)	40
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.5
No. Of switching cycles before premature failures	>50000
Inrush Current (A)	3
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	138
Max. Luminaires per 16A C Breaker	222
Max. Luminaires per 20A C Breaker	278

### Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

### Physical data

Nominal Product Length (mm)	104
Nominal Product Diameter (mm)	35
Weight (kg)	0.026

### Packaging

Single packaging type	Carton
Product EAN number	5410288275154
Packaging single length / height (cm)	10.2
Packaging single width (cm)	3.5
Packaging single depth (cm)	3.5
DUN14 (inner)	25410288275158
Units per inner package	6
Packaging inner length / height (cm)	11.5
Packaging inner width (cm)	8.0
Packaging inner depth (cm)	11.5
DUN14 (outer)	15410288275151
Units per outer package	60
Packaging outer length / height (cm)	42.5

## TOLEDO CANDLE

*ToLEDo CANDLE V6 470LM 840 E14 SL*

0027515

<b>Packaging outer width (cm)</b>	13.0
<b>Packaging outer depth (cm)</b>	25.5

### Safety data

<b>Breakage cleaning instructions</b>	Not applicable
<b>Special purpose lamp</b>	No
<b>Dry applications use only</b>	Yes
<b>Suitable for household illumination</b>	Yes
<b>Safety message</b>	Not Suitable for totally enclosed fixtures