

High-performance angular milling cutter 90°

For indexable milling inserts AD.X 0602..

ATORN[®]

Application

High-performance angular milling cutter 90°

Advantage

- Highly positive indexable insert
- Low power consumption
- precise 90° angular milling

Art. No.	16031 054
Cutting edge diameter	40 mm
Length	40 mm
Bore diameter	22 mm
max. ap	5.5 mm
Number of cutting edges	10 PCS



EAN-Code

4050293637410