

SVHB clamp holder, positive

For copy and longitudinal face turning using VB indexable inserts

ATORN[®]

Application

For copy, longitudinal and face turning with VB indexable insert, 35°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 107.5°, tip angle 35°, clearance angle 5°
- SVHBR 1212 F11

Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



Art. no.	17836 309
ISO name	SVHB R/L 2525 M16
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Length of head	20.6 mm
Programming size	32 mm
Suitable for indexable inserts	VB.. 1604..
Tool design	Left

EAN-Code

4050293563443