

Collet chuck shape E4 type ER

With collet chuck cylinder mount

ORION[®]

Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm²
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground
- Other designs available on request
- When selecting ER collet chucks, shape B should be used where possible



| | |
|---------------------------------|------------------|
| Art. no. | 22778 147 |
| Brand | ORION |
| Manufacturer Part Number | 22778147 |
| VDI mount diameter | 20 mm |
| Collet type | ER 32 |
| Min./max. clamping range | 2-20 mm |
| Projecting length | 50 mm |
| Outer diameter | 50 mm |
| Height | 23 mm |
| Length | 16 mm |
| Gross Weight | 0.750 kg |
| Product Group | 2AC |

EAN

4053625465354