

PVC workplace mats

Diamond plate structure, height 9 mm

Application:

Ideal for dry workstations and light- to medium-duty applications.

Version:

- Single-layer, ergonomic PVC mat with non-slip diamond plate surface
- Non-slip and impact resistant, insulates against cold and protects the industrial floor
- R10 slip resistance in accordance with EN 13552
- Fire protection class B2 according to DIN 54332/DIN 4102
- Weight approx. 3.5 kg/m²
- Ref. no. 164-167: with yellow safety marking strips on sides

Advantage:

- Relieves the back and leg muscles and prevents premature fatigue during extended periods of standing
- Increases general safety underfoot
- Easy to cut to the requested dimensions and shape

Delivery:

Mats delivered with bevelled edges, even if cut to size



Art. no.	50225 167
Surface structure	Stud plate / closed
Material	PVC - Polyvinyl chloride
Length	1000 mm
Width	1200 mm
Material thickness	9 mm
Mat design	Bulk stock
Min. temperature resistance	0 °C
Max. temperature resistance	60 °C
Suitable for wet areas	No
Antistatic	No
Anti-fatigue	Yes
Non-slip	Yes
Compliant with REACH	Yes
Colour	Black, Yellow

EAN-Code

5060 10353060 1