

MILAN S.r.l. a socio unico

Head Office – Export department:  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it



## Technical Datasheet

# tasker® C705 U.T.P. Cat. 5e

### 4x2x0,14 mm<sup>2</sup> - UL/ETL verified Cable



A	B	C	D
---	---	---	---

#### ETHERSOUND CATEGORY

Stranded conductors EIA/TIA 568-suitable not only for RJ 45 8 Pin.  
 Data Transmission Cable (See Audio Catalogue).

- A:** Grey Soft **PVC** Sheath. Outer cable Diam. Ø 6,00 (±0,10) mm.
- B:** The four pairs are stranded together with polyester based tape.
- C:** Insulation with PE – Diam. Ø 0,90 (±0,10) mm.  
 RJ45 plug connector compatible.  
 Core colors: White – Blue/Blue White-Orange/ Orange,  
 White Green/Green, White-Brown/Brown.
- D:** Stranded formation of 7x0,15 mm in O.F.C. Red Copper.  
 Nom. Cross section 4x2x0,14 mm<sup>2</sup>.

#### MARKING

**tasker® C705 E-TYPE CM 4x2x0,14 mm<sup>2</sup> 60°C (UL) E188630 CSA LL81295 FT4 ETL VERIFIED TO TIA/EIA-568-B.2 CAT.5e PATCH CABLE U.T.P. 13G1707141621**

#### CUSTOM

This product is also available in **L.S.Z.H.** polymer, **PE, PUR**, with or without **Steel Armor**.

#### Cable Properties

<b>Conductor Resistance</b>	140 Ω/Km ± 5%
<b>Impedance</b>	100 Ω± 5%
<b>Max Rated Voltage</b>	49 V
<b>Operative Temperature</b>	-15/+70°C

<b>USE</b>	<input checked="" type="checkbox"/>	Indoor	Interno Edificio	<b>INSTALLATION</b>	<input checked="" type="checkbox"/>	Fixed	Fissa	<b>INFORMATION</b>	<input checked="" type="checkbox"/>	RoHS2 Compliant
<b>Impiego</b>	<input checked="" type="checkbox"/>	Outdoor Limited	Esterno Limitato	<b>Posa</b>	<input checked="" type="checkbox"/>	Flexible Limited	Flessibilità limitata	<b>Informazioni</b>	<input checked="" type="checkbox"/>	Ver. C / 18.07.2016
		Outdoor Direct Burial	Esterno Interrato		<input checked="" type="checkbox"/>	Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			