

## PeakTech® TF-40 PROD-ID: P TF-40

### Liquid temperature probe, -50 ... +700 °C

This temperature probe is typ-K-thermocouples (NiCrNi). This probe is suitable for all of our thermometers published in our catalogue.



Model	P TF-40
Range	-50 °C.....+700 °C / -58 °F...+1250 °F
Accuracy	± 2 %
Cable length	175 cm
Probe length	162 mm
Probe	3,2 mm
EAN-13	4250569401664

