

Inline Fuse holder

∅ 5 x 20 mm/∅ 6.3 x 25 mm/∅ 6.3 x 32 mm



FEATURES:

Allows own choice of wire

Bayonet type cover

SPECIFICATION:

For fuses ∅ 5 x 20 mm/∅ 6.3 x 25 mm/∅ 6.3 x 32 mm

Assembly type Cable

Rated voltage 250 VAC

Nominal current 6.3 A

Contact material Brass, nickel-plated, tin-plated



Art. Nr.

RND 170-00170

