


STLZ950/..G-5.08-V-GREEN



Technical Data

Wire Sizes	Insulating Material
Solid min -	Material PA 6.6
solid max -	Flammability Class UL 94 V-0
Stranded (flexible) -	Temperatures
min -	Operating Temperature -30 °C - 105 °C
Stranded (flexible) -	Wave Soldering Process
max -	Soldering Temperature, recommended 265 °C
Stranded with Ferrule -	Peak Soldering Time, recommended 3-4 s
min -	Reflow Process
Stranded with Ferrule -	Soldering Temperature, recommended -
max -	Peak Soldering Time, recommended -
Dimensions	
Stripped Length	
PCB Hole Diameter 1.4 mm	
Materials	
Contact Pin Copper Alloy	

Colours


	GREEN, RAL6018
	BLACK, RAL9011
	BASALT GREY, RAL7012
	PEBBLE GREY, RAL7032
	LIGHT GREY, RAL7035
	LIGHT GREEN, similar RAL 6018

Colours according to RAL, there may be variations on colour due to production conditions. Special colours on request.

Counterparts (Spacing 5.08 mm)

Pin Strip/Terminal Blocks
AKZ950 STLZ950-INV AKZ4951 AKZ1200 AKZ1100

If there are combinations with different ratings, the lower value is valid.



Order Data (Spacing 5.08 mm)

Poles	Width (mm)	Article Designation	Article Number	PU
2	11.36	STLZ950/2G-5.08-V-GREEN	50950025121F	200
3	16.44	STLZ950/3G-5.08-V-GREEN	50950035121F	200
4	21.52	STLZ950/4G-5.08-V-GREEN	50950045121F	200
5	26.60	STLZ950/5G-5.08-V-GREEN	50950055121E	100
6	31.68	STLZ950/6G-5.08-V-GREEN	50950065121E	100
7	36.76	STLZ950/7G-5.08-V-GREEN	50950075121E	100
8	41.84	STLZ950/8G-5.08-V-GREEN	50950085121D	50
9	46.92	STLZ950/9G-5.08-V-GREEN	50950095121D	50
10	52.00	STLZ950/10G-5.08-V-GREEN	50950105121D	50
11	57.08	STLZ950/11G-5.08-V-GREEN	50950115121D	50
12	62.16	STLZ950/12G-5.08-V-GREEN	50950125121D	50
13	67.24	STLZ950/13G-5.08-V-GREEN	50950135121D	50
14	72.32	STLZ950/14G-5.08-V-GREEN	50950145121D	50
15	77.40	STLZ950/15G-5.08-V-GREEN	50950155121D	50
16	82.48	STLZ950/16G-5.08-V-GREEN	50950165121D	50
17	87.56	STLZ950/17G-5.08-V-GREEN	50950175121D	50
18	92.64	STLZ950/18G-5.08-V-GREEN	50950185121D	50
19	97.72	STLZ950/19G-5.08-V-GREEN	50950195121D	50
20	102.80	STLZ950/20G-5.08-V-GREEN	50950205121D	50
21	107.88	STLZ950/21G-5.08-V-GREEN	50950215121D	50
22	112.96	STLZ950/22G-5.08-V-GREEN	50950225121D	50
23	118.04	STLZ950/23G-5.08-V-GREEN	50950235121D	50
24	123.12	STLZ950/24G-5.08-V-GREEN	50950245121D	50

Accessories

Figure	Designation	Article Number
	Coding star CS2-5.0/5.08-RED	50000000024
	Dividing element SE-STL950-GREEN	50950000002



Ratings



Usegroup	B	C	D	
Rated Voltage	300 V	150 V	300 V	250 V
Rated Current	15 A	15 A	10 A	12 A
Overvoltage Category				III
Test Voltage	1.6 kV	1.6 kV	1.6 kV	4.0 kV
Pollution Degree				3