



Figure similar

SIMATIC HMI MEMORY CARD 512 MB SECURE DIGITAL CARD FOR MP 177, MP 277, MP 377, MOBILE PANEL 277, FROM WINCC FLEXIBLE 2008 SP1 FOR OP 77, TP/OP 177, TP/OP 277, MOBILE PANEL 177 AND ALL HMI PANELS WITH SD/MMC SLOT

Product type designation	
Installation type/mounting	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
Supply voltage	
Type of supply voltage	DC
Rated value (DC)	3.3 V
Input current	
Current consumption (rated value)	60 mA
Memory	
Type of memory	Secure Digital memory card
Memory size	512 Mbyte
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	50 °C
Storage/transport temperature	
• Min.	-20 °C
• max.	60 °C
Relative humidity	
• Operation, max.	90 %

Mechanics/material

Type of housing (front)

- plastic

Yes

Dimensions

Width

24 mm

Height

32 mm

Thickness

2.1 mm

Weights

Without packaging

3 g

Scope of supply

Delivery unit in items

1

other

Note:

for MP 177, MP 277, MP 377 and Mobile Panel 277, WinCC flexible 2008 SP1 and higher for OP 77, TP/OP 177, TP/OP 277, Mobile Panel 177, with SD/MMC slot

Usable in the following products

- Product 1
- Product 2
- Product 3
- Product 4
- Product 5
- Product 6
- Product 7
- Product 8
- Product 9
- Product 10
- Product 11
- Product 12
- Product 13
- Product 14
- Product 15
- Product 16
- Product 17
- Product 18
- Product 19

[6AV6642-0EA01-3AX0](#)

6AV6643-0C*

6AV6643-0D*

6AV6643-7D*

6AV6643-7C*

6AV6643-8*

6AV6644-*

[6AV6645-0BE02-0AX0](#)

6AV6645-0C*

6AV6645-0D*

6AV6645-0E*

6AV6645-0F*

6AV6645-0G*

6AV6641-0B*

6AV6641-0C*

6AV6642-0*

[6AV6643-0AA01-1AX0](#)

[6AV6643-0BA01-1AX0](#)

6AV6643-7BA*

last modified:

12.03.2015