


CUSTOMER	CPC
ITEM NO.	CS145** Series



SIDE:A

SIDE:B

NOTE:

(1). Cable Wiring: UL2919 28#\*3COAX+30#\*4C+AL+1+B(96CU)  
 Jacket Material: PVC OD: 8.0 ± 0.2mm  
 Cable Colour: Black  
 Cable Printing: E119932-T AWM 2919 80° 30V VW-1 LOW VOLTAGE  
 COMPUTER CABLE COPARTNER

(2). Connector A: HDB 15PIN Male Solder Type  
 Insulation: Black  
 Contact: Gold Plated 3u''  
 Shell: Nickel/Sn Plated

(3). Connector B: HDB 15PIN Male Solder Type  
 Insulation: Black  
 Contact: Gold Plated 3u''  
 Shell: Nickel/Sn Plated

(4). Thumb Screw: 4.5\*48.5mm Nickel Plated

(5). Core Spc: ∅17.5\*∅9.5\*28.5mm

(6). Over Mold 1 Colour: PVC-60P-Black

(7). Over Mold 2 Colour: PVC-25P-Black

(8). Parameter Settings: CT-8681FA

1. Conductive Resistance: 5.0 Ω
2. Insulative Resistance: 5.0M Ω
3. Hi-Pot: 300V/AC, DC, 1.5mA/I, 50Hz, 0.01s

(9). ALL COMPONENTS ARE RoHS COMPLIANT.


(10). 100% OPEN AND SHORT TEST

(11). Packing: PEBAG Packing

ITEM NO.	CS14509	CS14510	CS14511	CS14512	CS14513	CS14514	CS14515	CS14516	CS14517	CS14518
L ± T (mm)	500	1000	2000	3000	5000	10000	15000	20000	30000	40000
PRODUCT NO.	VC00305-BK	VC0031-BK	VC0032-BK	VC0033-BK	VC0035-BK	VC00310-BK	VC00315-BK	VC00320-BK	VC00330-BK	VC00340-BK
FERRITES	NO	NO	NO	NO	NO	YES	YES	YES	YES	YES

SIDE:A HD15M	SIDE:B HD15M	SIDE:A HD15M	SIDE:B HD15M
1 — RED	1 — RED	5 —	5 —
6 — RED	6 —	10 —	10 —
2 — GREEN	2 —	13 —	13 —
7 — GREEN	7 —	14 —	14 —
3 — BLUE	3 —	DRAIN —	DRAIN —
8 — BLUE	8 —		

PIN OUT: (8)



PACKING: (11)

GENERAL TOLERANCES (UNLESS SPECIFIED)					
LENGTH: X ± 1 .X ± 0.2 .XX ± 0.10		UNIT: mm	REV: 00		
ANGLE: X° ± 1° .X° ± 0° 30'		DRAWING	XIAODENG	2014/07/18	S. P. NO.
		CHECK			HT-5919
		APPROVE			NAME
					HD 15PM/HD 15PM
					DWG. NO.
					PAGE
					1/1

01	NEW	2014/07/21
REV	DESCRIPTION	DATE