




Surface mounting enclosure, flat, 3 mounting locations, M30

Part no. **M30-FI3**
 Catalog No. **197237**

Delivery program

Basic function accessories			Surface mounting enclosure
Housing			Insulated material
			With high-grade steel screws
Number of locations		Qty.	3
Cable entry knockouts			
Cable entry			rear: 1 x M20 lateral: 2 x M20 (1 x each side)
Degree of Protection			IP66, IP67, IP69
Impact resistance			IK06 according to EN 50102
Colour			
			
RAL Value			RAL 7035
Colour			Enclosure base anthracite
Connection to SmartWire-DT			no
For use with			3 x Ø 30.5
For use with			(Illuminated) pushbuttons (Illuminated) selector switches Key-operated pushbuttons Indicator light EMERGENCY STOP/EMERGENCY OFF buttons with yellow set of adapter rings M22Y-R30 Flat rear contact elements M22-FK... Flat Rear LED elements M22-FLED-...
Actuator travel and actuation force as per DIN EN 60947-5-1, K.5.4.1			
Minimum force for positive opening	N		0

Technical data

General			
Degree of Protection			IP66, IP67, IP69
Ambient temperature			
Open		°C	-25 - +70

Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70
Impact resistance			IK06 according to EN 50102

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Enclosure for control circuit devices (EC000200)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Housing for command and alarm devices (ecI@ss10.0.1-27-37-12-05 [AKF023014])			
Number of command positions			3
Construction type housing			Surface mounting housing
Material housing			Plastic
Material quality housing			Other
Diameter openings		mm	30
Colour housing cover			Grey
Degree of protection (IP)			IP67/IP69K
Degree of protection (NEMA)			
Width		mm	43
Height		mm	244
Depth		mm	44

Dimensions

