



- Constructed of heavy duty 14 gauge steel.
- Front & rear lip folded for extra strength.
- Versatile design can be used upside down (front & rear lip become equipment retainers).
- Sides folded up for easy hardware installation from above.
- Sides are slotted for easy adjustment with most rail depth locations.
- Rugged textured powder paint finish.
- Tested to nearly double the suggested load rating of 350 lbs.
- Includes all mounting hardware.
- RoHS and REACH compliant.
- Manufactured in North America.

Please note that to mount this product you need to have two (2) pairs of combination rails within your cabinet. This product does not mount to the front and back of the rails like traditional rack mounting shelves. If used with our CPR square hole rails you will need to order CPRSA rail adaptor for each shelf ordered.

Accessories

- Fixed Shelf Rail Adapter
- Hook and Loop Roll

Solid	Vented	Overall Dimensions			
Part No.	Part No.	Height	Flange Height	Width	Depth
RFUS1918BK1	RFVS1918BK1	1.94	0.81	17.75	18.00
RFUS1921BK1	RFVS1921BK1	1.94	0.81	17.75	21.00
RFUS1926BK1	RFVS1926BK1	1.94	0.81	17.75	26.00
RFUS1931BK1	RFVS1931BK1	1.94	0.81	17.75	31.00

Data subject to change without notice

 $\ensuremath{\mathbb{C}}$ 2016. Hammond Manufacturing Ltd. All rights reserved.



HAMMOND MANUFACTURING.





