

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2162701080](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Cable Assemblies](#)  
**Description:** SL Female-to-SL Female Off-the-Shelf (OTS) Cable Assembly, Positive Lock, Single Row, 50.00mm Length, Tin (Sn) Plating, 8 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">216270</a>
Application	Signal, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	SL-to-SL
Overview	<a href="#">Off-the-Shelf Cable Assemblies</a>
Product Name	SL
Type	Discrete Wire Assembly
UPC	193264730797

**Physical**

Cable Length	50.00mm
Circuits (Loaded)	8
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Net Weight	4.809/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.63mm max.
Wire Size AWG	22
Wire/Cable Type	UL 11028

**Electrical**

Current - Maximum per Contact	3.0A
Voltage - Maximum	600V AC/DC

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	2162701080-000
---------------	----------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[216270 Series](#)