

G83-6104/G83-6105



Models may vary from the image shown

Proven millions of times over!

There's a reason why this keyboard has been one of the most reliable and successful on the market for many years, with more than 30 million satisfied users.

Key benefits

- NTK technology (elastomer keys with membrane contact switches)
- Space-saving, compact design
- Long-lived and recycling-friendly
- Comfortable actuation
- Uniform switching characteristics
- Abrasion-proof inscription of key caps

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

Product dependant, see table "Models"

Key colour:

Product dependant, see table "Models"

Weight (product):

662 g

Total weight (with packaging):

810 g

Cable Length:

approx. 1.75 m

Storage Temperature:

-20°C to 60°C

Operating Temperature:

0°C to 50°C

Current Consumption:

typ. 16 mA

Interface:

Product dependant, see table "Models"

Product approvals:

- cURus 
- VDE GS 
- c-tick 
- GOST-R 
- CE 
- FCC 

System requirements:

Product dependant, see table "Models"

Delivery Volume:

- G83-6104/G83-6105
- Printed instructions

Dimensions (product):

approx. 458 x 170 x 42 mm

Packaging dimensions:

approx. 493 x 210 x 47 mm

Keyboard:

- Key technology: NTK
- Service life, standard key: > 20 million key operations
- Operation characteristics: Soft pressure point
- Inscription technology: Laser
- Inscription layout: Normal
- Number of Keys: Product dependant, see table "Models"

Packaging Unit:

- Number of products in the master package: 65
- Number of master packages per pallet: 2

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted.
Technical information refers only to the specifications of the products. Features may differ from the information provided.