

Roughing cutter HSSE Co 5

4 flutes, uncoated

ORION[®]

Application:

End mill for universal machining in diverse materials.

Execution:

- HSSE Co 5
- Centre cutting
- Straight shank in accordance with DIN 1835 D
- Type NR
- Roughing teeth



Art. no.	15242 140
Brand	ORION
Manufacturer Part Number	15242140
Cutting material	HSSE Co5
Surface	Uncoated
Type	NR
Number of cutting edges	4 PCS
Twist angle	30°
Edge protection chamfer length	0.2 mm
Tool holding device	HD parallel shank
Construction length	Long
Cutting edge diameter	14 mm
Cutting edge length	53 mm
Length	110 mm
Shank diameter	12 mm
fz steel 700	0.073 mm
Gross Weight	0.100 kg
Product Group	106

EAN

4039247093243