

## “Schmiermeister“ pneumatic grease systems

For greases and viscous oils



### Application:

For mobile lubrication of equipment and machinery

### Execution:

- Pressure ratio 55:1, air pressure min./max.: 6 bar/ 10 bar
- Pump type: Double-acting, displacement volume approx. 600 g/min
- Working/bursting pressure: 400 bar/1600 bar
- Pump output and compressed air connection 1/4"
- Portable: Robust trolley with 2 driving and 2 steering wheels
- For 15/18 kg drums

### Delivery:

Grease pump with pre-conveyor system Pressure reducer/water separator Grease follower cover Steel dust cover with integrated barrel screw joint 4 m safety high-pressure lubrication hose (1600 bar) High-pressure grease gun with 360° swivel joint



<b>Art. no.</b>	<b>56260 100</b>
<b>Brand</b>	SAMOA-HALLBAUER
<b>Manufacturer Part Number</b>	40260
<b>Max. operating pressure</b>	400 bar
<b>Suitable for container contents</b>	15 l
<b>Gross Weight</b>	17.000 kg
<b>Product Group</b>	SIG

### EAN

4024937402603