

Wiha articulated hose system.

The universal pipe system.



maxiflex® programme ø 1/4" (6.35 mm).

Order-No.	Article-No.	Image
27085 8	412 2030	
		Pack with 22 segments, assembled Length: 280 mm
27086 5	412 2060	
		Pack with 80 segments, assembled Length: 1000 mm
27087 2	412 2220	
		Pack with 4 cylindrical nozzles ø 1.6 mm
27088 9	412 2240	
		Pack with 4 cylindrical nozzles ø 3.2 mm
27089 6	412 2260	
		Pack with 4 cylindrical nozzles ø 5.6 mm
27090 2	412 2280	
		Pack with 2 flat nozzles 24 mm wide
27091 9	412 2330	
		Pack with 2 flat nozzles 24 mm wide
27092 6	412 2420	
		Pack with 4 angular nozzles ø 1.6 mm
27093 3	412 2440	
		Pack with 4 angular nozzles ø 3.2 mm
27094 0	412 2460	
		Pack with 4 angular nozzles ø 5.6 mm
27095 7	412 2480	
		Pack with 2 multi-hole angular nozzles, 7 holes (ø 2 mm)
27096 4	412 2640	
		Pack with 4 adapters for LOC-LINE® Flexi and ARIANA Cool-Line
27097 1	412 2650	
		Pack with 4 spherical double socket segments
27098 8	412 2660	
		Pack with 4 double nipples
27099 5	412 2710	
		Pack with 4 threaded nipples R 1/8"
27100 8	412 2720	
		Pack with 4 threaded nipples R 1/4"
27101 5	412 2740	
		Pack with 2 Y-junctions
27102 2	412 2770	
		Pack with 2 regulating valves
27103 9	412 2780	
		Pack with 2 segment clips
28006 2	412 2020	
		6 short nozzles, assembled, with: 1 threaded nipple R 1/8" 1 segment 1 short cylindrical nozzle ø 2.5 mm
29446 5	412 2760	
		Ball valve with threaded outlet G 1/4"

maxiflex® programme ø 1/4" (6.35 mm).

Order-No.	Article-No.	Image
27084 1	412 2010	
		maxiflex®-set, assembled 1 threaded nipple R 1/4" 22 segments 1 cylindrical nozzle ø 3.2 mm Total length: 320 mm
27108 4	412 2920	
		Separation wedge
27109 1	412 2930	
		Assembly pliers
27104 6	412 2810	
		Set with magnetic foot and ball valve, assembled 1 threaded nipple R 1/4" 22 segments 1 cylindrical nozzle ø 3.2 mm Magnetic foot with hose nozzle ø 11 mm Extra: Magnetic adhesion 80 N
27105 3	412 2820	
		Set with magnetic foot, assembled 2 threaded nipples R 1/4" 44 segments, length: 2 x 320 mm 2 cylindrical nozzles ø 3.2 mm Magnetic foot with hose nozzle ø 11 mm Extra: Magnetic adhesion 80 N
27106 0	412 2830	
		Set with magnetic foot and ball valve, assembled 1 threaded nipple R 3/8" for hose diameter 1/2" 1 reduction of hose diameter from 1/2" to 1/4" 22 segments 1 cylindrical nozzle ø 3.2 mm Magnetic foot with hose nozzle ø 11 mm Extra: Magnetic adhesion 150 N
27107 7	412 2850	
		Distribution block with 3 ball valves Ball valves with threaded outlets R 1/4" Hose nozzle ø 11 mm Extra: Magnetic adhesion 4 x 95 N
30518 5	412 2000	
		maxiflex® basic set 3 tubes à 280 mm 2 cylindrical nozzles ø 1.6 mm 3 cylindrical nozzles ø 3.2 mm 2 cylindrical nozzles ø 5.6 mm 1 flat nozzle 24 mm 1 flat nozzle 24 mm, 7 holes ø 1.5 mm 2 Y-junctions 1 spherical double socket segment 2 threaded nipples R 1/8" 3 threaded nipples R 1/4" 1 adapter for LOC-LINE® 1 assembly pliers 1 separation wedge

maxiflex® programme ø 1/2" (12.7 mm).

Order-No.	Article-No.	Image
27111 4	412 4030	
		Pack with 12 segments, assembled Length: 265 mm
27112 1	412 4060	
		Pack with 48 segments, assembled Length: 1000 mm
27113 8	412 4130	
		Pack with 4 jointed pipe segments Length: 440 mm
27114 5	412 4160	
		Pack with 4 segment clips incl. screws
27115 2	412 4220	
		Pack with 4 cylindrical nozzles ø 10 mm
27116 9	412 4240	
		Pack with 2 flat nozzles, 6 holes (ø 10 mm) 30 mm wide
27117 6	412 4330	
		Pack with 2 flat nozzles 30 mm wide
27118 3	412 4360	
		Pack with 2 flat nozzles 60 mm wide
27119 0	412 4420	
		Pack with 4 angular nozzles ø 7 mm
27120 6	412 4440	
		Pack with 4 angular nozzles ø 10 mm
27121 3	412 4460	
		Pack with 2 multi-hole angular nozzles, 8 holes (ø 3.5 mm)
27122 0	412 4620	
		Pack with 2 reducers, 1/2" to 1/4" system
27123 7	412 4640	
		Pack with 4 adapters for LOC-LINE® Flexi and ARIANA Cool-Line
27124 4	412 4650	
		Pack with 4 spherical double socket segments
27125 1	412 4660	
		Pack with 4 double nipples
27126 8	412 4720	
		Pack with 4 threaded nipples R 3/8"
27127 5	412 4730	
		Pack with 4 threaded nipples R 1/2"
27128 2	412 4740	
		Pack with 2 Y-junctions
27129 9	412 4750	
		Pack with 2 Y reducer junctions 1/2" to 1/4" system
27130 5	412 4770	
		Pack with 2 regulating valves
27131 2	412 4780	
		Pack with 2 segment clips

maxiflex® programme ø 1/2" (12.7 mm).

Order-No.	Article-No.	Image
29447 2	412 4760	
		Ball valve with threaded outlet G 3/8"
27110 7	412 4010	
		maxiflex®-set, assembled 1 threaded nipple R 1/2" 12 segments 1 cylindrical nozzle ø 10 mm Total length: 320 mm
27134 3	412 4920	
		Separation wedge
27135 0	412 4930	
		Assembly pliers
27132 9	412 4820	
		Set with magnetic foot and ball valve, assembled 1 threaded nipple R 3/8" 12 segments 1 cylindrical nozzle ø 10 mm Magnetic foot with hose nozzle ø 13 mm Extra: Magnetic adhesion 150 N
27133 6	412 4860	
		Distribution block with 3 ball valves Ball valve with threaded outlet R 3/8" Extra: Magnetic adhesion 4 x 95 N
30519 2	412 4000	
		maxiflex® basic set 3 tubes à 265 mm 3 cylindrical nozzles ø 10 mm 1 flat nozzle 30 mm 1 flat nozzle 60 mm 1 flat nozzle 30 mm, 6 holes ø 3.3 mm 1 Y-junction 1 Y reducer junction 1 reduction of hose diameter from 1/2" to 1/4" 3 threaded nipples R 1/2" 2 threaded nipples R 3/8" 1 adapter for LOC-LINE® 1 assembly pliers 1 separation wedge

Wiha Info

You currently use a different system?
No problem!

System	Information
LOC-LINE®	Compatible with help of maxiflex® adapter order no. 27096 (1/4") and 27123 (1/2").
Snap-Loc®	Compatible on both sides (external and internal ball) without adapter.
ARIANA Cool-Line	Compatible with help of maxiflex® adapter order no. 27096 (1/4") and 27123 (1/2").
LEGROM-VARIO-System®	Small version 1/4" is compatible with help of maxiflex adapter (order no. 27096) when using Varios outer ball and adapters inner ball.