

STANDARD EXECUTIONS

- **GN 5435-MT-H:** AISI 316L stainless steel, sandblasted matte finish.
- **GN 5435-PL-H:** AISI 316L stainless steel, mirror polished finish (RA < 0,8μ).

PACKING RING

H-NBR synthetic rubber hardness 85 +/-5 Shore A, blue colour, in compliance with FDA.


FEATURES AND APPLICATIONS

GN 5435 lobe knobs are intended for use in environments where high hygiene is required.

The presence of the special packing ring seals the thread from the external environment, preventing the access of impurities.

The finish quality, angular seal and absence of recesses, prevents dirt adherence and facilitates cleaning.

See Hygienic Design technical data (on page 1186).



GN 5435-MT-H

INOX STAINLESS STEEL

Code	Description	d1	d2	d3	d4	h1	h2	t	⚖️
GN.23301	GN 5435-40-M6-MT-H	40	M6	18	18.8	30.5	15	12	136
GN.23311	GN 5435-40-M8-MT-H	40	M8	18	18.8	30.5	15	15	132
GN.23321	GN 5435-50-M8-MT-H	50	M8	21	21.8	34	17	15	231
GN.23331	GN 5435-50-M10-MT-H	50	M10	21	21.8	34	17	18	226

GN 5435-PL-H

INOX STAINLESS STEEL

Code	Description	d1	d2	d3	d4	h1	h2	t	⚖️
GN.23306	GN 5435-40-M6-PL-H	40	M6	18	18.8	30.5	15	12	136
GN.23316	GN 5435-40-M8-PL-H	40	M8	18	18.8	30.5	15	15	132
GN.23326	GN 5435-50-M8-PL-H	50	M8	21	21.8	34	17	15	231
GN.23336	GN 5435-50-M10-PL-H	50	M10	21	21.8	34	17	18	226

