



**BRIDA DE AMARRE RÁPIDO**

Apriete Vertical con Mango Horizontal

Horizontal toggle clamp

Sauterelle à levier horizontal



| Ref.   | A (mm) | B (mm) | C (mm) | D (mm) | E (mm) | F (mm) | G (mm) | H (mm) | T (mm) | K (mm) | d (mm) | Presión en Kg. |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|----------------|
| 5002-1 | 195    | 53     | 40     | 56     | 44     | 6      | 41     | 28     | 14     | 5,5    | 8      | 200            |
| 5002-2 | 300    | 115    | 60     | 80     | 60     | 10     | 56     | 36     | 20     | 8,5    | 12     | 300            |
| 5002-3 | 410    | 150    | 75     | 96     | 76,5   | 10     | 64     | 45     | 20     | 8,5    | 14     | 450            |
| 5002-4 | 550    | 210    | 115    | 132    | 102    | 15     | 85     | 55     | 30     | 13     | 16     | 600            |