


Part Number: TB01XXXX

| Type | Size | Rating | Description |
|------|------|---------|--------------------------------------|
| LED | 8mm | Various | Recessed Bezel LED with flying leads |

All dimensions in mm.



| Part no. | Length L | Colour | Volts | Current mA | Intensity mcd | LED |
|----------|----------|--------|-----------|------------|---------------|----------|
| TB010005 | 500 | red | $V_f=2.0$ | 20 | 50 | standard |
| TB010009 | 900 | red | $V_f=2.0$ | 20 | 50 | standard |
| TB010015 | 500 | green | $V_f=2.0$ | 20 | 40 | standard |
| TB010019 | 900 | green | $V_f=2.0$ | 20 | 40 | standard |
| TB010025 | 500 | yellow | $V_f=2.1$ | 20 | 40 | standard |
| TB010029 | 900 | yellow | $V_f=2.1$ | 20 | 40 | standard |
| TB010105 | 500 | red | 6DC | 16 | 40 | standard |
| TB010115 | 500 | green | 6DC | 16 | 32 | standard |
| TB010125 | 500 | yellow | 6DC | 16 | 32 | standard |
| TB010205 | 500 | red | 12DC | 16 | 40 | standard |
| TB010209 | 900 | red | 12DC | 16 | 40 | standard |
| TB010215 | 500 | green | 12DC | 16 | 32 | standard |
| TB010219 | 900 | green | 12DC | 16 | 32 | standard |
| TB010225 | 500 | yellow | 12DC | 16 | 32 | standard |
| TB010229 | 900 | yellow | 12DC | 16 | 32 | standard |
| TB010305 | 500 | red | 24DC | 10 | 25 | standard |
| TB010309 | 900 | red | 24DC | 10 | 25 | standard |
| TB010315 | 500 | green | 24DC | 10 | 20 | standard |
| TB010319 | 900 | green | 24DC | 10 | 20 | standard |
| TB010325 | 500 | yellow | 24DC | 10 | 20 | standard |
| TB010329 | 900 | yellow | 24DC | 10 | 20 | standard |
| TB011005 | 500 | red | 3.5-13DC | 22@9V | 40@9V | flashing |
| TB011009 | 900 | red | 3.5-13DC | 22@9V | 40@9V | flashing |
| TB011015 | 500 | green | 3.5-13DC | 22@9V | 40@9V | flashing |
| TB011019 | 900 | green | 3.5-13DC | 22@9V | 40@9V | flashing |
| TB011025 | 500 | yellow | 3.5-13DC | 22@9V | 40@9V | flashing |
| TB011029 | 900 | yellow | 3.5-13DC | 22@9V | 40@9V | flashing |
| TB011305 | 500 | red | 24DC | 22 | 40 | flashing |
| TB011309 | 900 | red | 24DC | 22 | 40 | flashing |
| TB011315 | 500 | green | 24DC | 22 | 40 | flashing |
| TB011319 | 900 | green | 24DC | 22 | 40 | flashing |
| TB011325 | 500 | yellow | 24DC | 22 | 40 | flashing |
| TB011329 | 900 | yellow | 24DC | 22 | 40 | flashing |