


**WISKA COMBI 1210**



- |  |   |
|--|---|
| <b>Protection class to EN 60 529:</b>    | IP 66/67  |
| <b>Flame protection:</b>                 | Glow wire test 750 C acc. to EN 60695-2-11  |
| <b>Temperatures during installation:</b> | -5°C to 60°C  |
| <b>Temperature range of material:</b>    | -30°C to 100°C, intermittent up to approx. 120°C  |
| <b>Voltage:</b>                          | 690 V   |
| <b>Material:</b>                         | Polypropylene, reinforced; Sealing: thermoplastic elastomere  |
| <b>Terminals/poles:</b>                  | 10 mm <sup>2</sup>  |
| <b>Fixing:</b>                           | 4 internal openings outside of the sealing area   |
| <b>Equipment:</b>                        | <ul style="list-style-type: none"> <li>- 10 M 20 inputs with elastic soft membrane and thread, and M 25 breakout opening</li> <li>- 4 inputs with self-sealing ground membrane</li> <li>- 4 captive quick-release lid screws</li> <li>- Colour RAL 7035 light grey</li> <li>- .../S = black</li> <li>- .../W = white</li> </ul> |

Type	WISKA-No.					L x B x H external / außen mm
			mm			
COMBI 1210/5	10101462	2	3 - 12			160 x 140 x 81
COMBI 1210/5/S	10101463	2	3 - 12			160 x 140 x 81
COMBI 1210/5/W	10101464	2	3 - 12			160 x 140 x 81
DIN RAIL KIT 1210	10101478	1	-			-