

Specifications:

Impedance (Ω)	$8 \pm 15\%$ at 800 Hz at 1.0 V
Rated Power (W)	2.0
Max Power (W)	3.0
Resonance Freq Fo (Hz)	$420 \pm 20\%$ at 1.0 V
Frequency Range (Hz)	Fo ~ 9000
Output S.P.L. (dB)	107 ± 3 at 2.0w/1m 1.0k, 1.4k, 1.7k, 2.0kHZ 84 ± 3 at 1w/1m 1.0k, 1.4k, 1.7k, 2.0kHZ
Frame Material	Metal
Operating Temp	-20 to 55°C
Weight (g)	92.3
Options	For other options contact factory

Dimensions: ± 0.5 (units: mm)

ROHS Compliant

