


Reflector & Linear



- 2,000hr Lamp Life
- Clear Finish
- UV Stop Glass
- Dimmable
- Internal Fuse
- E27, E14 7 R7 Caps
- 25W - 500W Replacements

R39, R50, R63 & R80 - 2,000

Box Code	Blister Code	Finish	Cap	Watt. & Equiv.	Lumen	Colour Temp.	Dimmable	Lamp Dims. (mm)	In/Out Box	In/Out Blister
S11883	S11884 (2pk)	Clear	E14	20W/25W	235lm	2900K	✓	39x80	10/100	10/100
S10138	S11885 (2pk)	Clear	E14	30W/40W	405lm	2900K	✓	50x80	10/100	10/100
S10139	S11886 (2pk)	Clear	E27	46W/60W	700lm	2900K	✓	63x104	10/100	10/100
S10140	S11887 (1pk)	Clear	E27	46W/60W	700lm	2900K	✓	80x118	10/100	10/100

LINEAR - 2,000 HOURS

Box Code	Blister Code	Finish	Cap	Watt. & Equiv.	Lumen	Colour Temp.	Dimmable	Lamp Dims. (mm)	In/Out Box	In/Out Blister
S10112	S11853 (2pk)	Clear	R7	120W/150W	2250lm	2900K	✓	8x78	10/500	10/500
S10113	S11854 (2pk)	Clear	R7	160W/200W	3150lm	2950K	✓	8x118	10/500	10/500
S10114	S11855 (2pk)	Clear	R7	230W/300W	4700lm	2950K	✓	8x118	10/500	10/500
S10115	S11856 (2pk)	Clear	R7	400W/500W	8700lm	2950K	✓	8x118	10/500	10/500

