



## RLS4FC

4 pole loudspeaker cable connector with latch lock, chuck and bushing, bulk packed, to be ordered in multiples of 100 pcs.

### Article Variations

Article Name	Details	Packaging
RLS4FC	4 pole loudspeaker cable connector	BULK
RLS4FC-D	4 pole loudspeaker cable connector	BULK

## Technical Information

### Product

<b>Title</b>	RLS4FC
<b>Connection Type</b>	Loudspeaker Connectors

### Electrical

<b>Contact resistance</b>	≤ 5 mΩ (after lifetime)
<b>Dielectric strength</b>	4 kVdc (peak)
<b>Insulation resistance</b>	> 1 GΩ (after dampheat test)
<b>Rated current per contact</b>	30 A
<b>Rated voltage</b>	250 V (insulation)
<b>Attention</b>	Shall NOT be used as an AC mains connector!

### Mechanical

<b>Cable O.D.</b>	6 - 10 mm
<b>Lifetime</b>	> 1000 mating cycles
<b>Wiresize</b>	4 mm <sup>2</sup>
<b>Wiresize</b>	12 AWG

### Environmental

<b>Temperature range</b>	-30 °C to +80 °C
--------------------------	------------------