

## Inset Trend 62 Flush

*INSET TREND 62 FL ES50 BN EX-LMP*  
3083560



### Product features

- 62mm cut out. Fixed. Round bezel. Brushed Nickel



## PRODUCT OVERVIEW

Product name	INSET TREND 62 FL ES50 BN EX-LMP
Technology	LED/Halogen
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number SE	7464260
Warranty	3 years
LOR (%)	Dependent on lamp
Light colour	N/A
Light source included	Fixture without Lightsource
Electrical protection	Class II
Housing colour	Nickel
IP rating	IP20
IK rating	IK02
Product EAN number	8711971835608

## DATA TABLE

### General data

Product name	INSET TREND 62 FL ES50 BN EX-LMP
Technology	LED/Halogen
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number SE	7464260
Warranty	3 years

### Optical data

LOR (%)	Dependent on lamp
---------	-------------------

## Inset Trend 62 Flush

*INSET TREND 62 FL ES50 BN EX-LMP*  
3083560

Light colour	N/A
Adjustable chromaticity	N

### Electrical data

Light source included	Fixture without Lightsource
Mains voltage (V)	220-240V
Electrical protection	Class II
Transformer required	No
Nominal Frequency (Hz)	50/60Hz

### Physical data

Housing colour	Nickel
IP rating	IP20
IK rating	IK02
Nominal Product Length (mm)	82
Nominal Product Width (mm)	82
Nominal Product Height (mm)	85
Cutout Dimensions (W x L in mm or Diameter in mm)	62
Weight (kg)	0.104
Recessed Depth (mm)	85

### Packaging

Single packaging type	Carton
Product EAN number	8711971835608
Packaging single length / height (cm)	13.3
Packaging single width (cm)	10.17
Packaging single depth (cm)	7.0
DUN14 (outer)	18711971835605
Units per outer package	30
Packaging outer length / height (cm)	24.1
Packaging outer width (cm)	29.0
Packaging outer depth (cm)	53.4

## TECHNICAL DRAWINGS

