

## Adjustable clamps

Angled



### Application:

For clamping workpieces.

### Execution:

- With support screw and clamping screw
- Made from heat-treated steel
- Painted

<b>Art. no.</b>	<b>26221 010</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	70268
<b>For table grooves according to DIN 650</b>	10 mm
<b>Suitable screw DIN 787</b>	M10 x 80 mm
<b>Min./max. clamping range</b>	8-32 mm
<b>Groove width</b>	11 mm
<b>Span iron length</b>	80 mm
<b>Span iron width</b>	30 mm
<b>Thread dimension</b>	M10
<b>Thread length</b>	39 mm
<b>Thickness</b>	15 mm
<b>Distance</b>	15 mm
<b>Length</b>	30 mm
<b>Gross Weight</b>	0.349 kg
<b>Product Group</b>	260



### EAN

4020772070267

