

Adjustable clamps

Angled



Application:

For clamping workpieces.

Version:

- With support screw and clamping screw
- Made from heat-treated steel
- Painted

Art. no.	26221 010
For table grooves according to DIN 650	10 mm
Suitable screw DIN 787	M10 x 80 mm
Min./max. clamping range	8-32 mm
Groove width	11 mm
Span iron length	80 mm
Span iron width	30 mm
Thread dimension	M10
Thread length	39 mm
Thickness	15 mm
Distance	15 mm
Length	30 mm



EAN-Code

4020772070267