

Ergonomic WG workbench with electric height adjustment

Solid beech, 2,000 mm, height-adjustable via a control panel

Execution:

- Base made of square steel tube, outer 60 x 60 x 2 mm, inner 55 x 55 x 2 mm, with level compensation on all four feet
- Height infinitely adjustable from approx. 740-1040 mm via an electric control panel
- One perforated metal panel wall on both the right and left end faces of the workbench
- Fully assembled

Advantage:

- Workbench can be quickly and easily adjusted to the desired working height
- Always working at the right height ensures ideal ergonomic conditions
- Up to 4 different work heights are programmable and accessible at the touch of a button thanks to the memory function
- When you buy this product, you plant a tree and also receive a tree certificate!



Art. no.	50185 043
Number of drawers	2 PCS
Worktop width	2000 mm
Pullout type	Full extension
Worktop height	50 mm
Colour of front	Anthracite grey RAL 7016
Worktop depth	700 mm
Cabinet colour	Light grey RAL 7035
Functions	RFID possible
Max. height	1040 mm
Min. height	740 mm
Adjustable in height	Yes
Drawer surface	0.27 m ²
Surface	Powder-coated
With single pull-out safety brake	Yes
Load-carrying capacity	800 kg
Lock type	DOM® locking system
Drawer front height	2 x 90 mm
Dynamic load-carrying capacity	400 kg
Drawer width (inner dimension)	450 mm
Type	Electrical height adjustment
Drawer width (inner dimension) x drawer depth (inner dimension)	450 x 600 mm
Material of worktop	Solid beech
Drawer depth (inner dimension)	600 mm
Load-carrying capacity per drawer	70 kg
Material of base frame	Steel plate
Central locking	Yes
Levelling	Yes
Product Group	Prod. Gr. 5BC

EAN

4053625402250