

# Selection Guide for EIS Accessories

Photo	Part number	Description	Target application	MI 3155	MI 3152	MI 3152H	MI 3102 BT	MI 3102H BT	MI 3100 SE	MI 3125 BT	MI 3108	MI 3109	MI 3121	MI 3122	MI 3123	MI 3110	MI 2088	MI 2093	A 1143	
	A 1143	Euro Z 290 A	Euro Z 290 A is the impedance tester which enables line / loop impedance measurements with an accuracy down to 0.1 mΩ.	•	•	•														
	A 1532	A 1532 EVSE adapter	EVSE (Electric Vehicle Supply Equipment) adapter is a special accessory intended for testing Mode 3 EV supply equipment with a type 2 connector.	•	•	•	•	•	•	•										
	A 1199	Ro-adapter	Ro-adapter is intended for performing earth resistance measurement in combination with installation safety tester.	•	•	•	•	•												
	A 1378	EurotestPV Remote	PV remote unit for measurement and logging of irradiance and temperature values.								•	•								
	A 1384	PV Safety Probe	The PV safety probe can safely disconnect the PV installation from the installation in case of a permanent short circuit.								•	•								
	CS 2099	Eurocheck	Eurocheck is a professional multifunctional field calibrator intended for use with installation safety testers.		•		•	•	•	•			•	•	•					•
	A 1160	Fast charger for 8 AA batteries with a set of 6 NiMH bat., type AA	Fast battery charger for up to 8 pieces of AA rechargeable batteries, and a set of 6 pcs NiMH rechargeable batteries, type AA.		•	•	•	•	•	•	•	•	•	•	•	•	•			•
	A 1169	Fast charger for AA, C, D and 9 V block batteries	Fast battery charger for up to 12 pcs AA, 6 pcs C or D rechargeable batteries, 4 pcs 9 V block batteries.		•	•	•	•	•	•	•	•	•	•	•	•	•			•
	A 1135	Power supply adapter 12 V / 1,2 A	Adapter for fast battery charging.		•	•														
	A 1548	Power supply adapter 12 V / 0,5 A					•	•	•	•	•	•	•	•	•	•	•			
	A 1569	Power supply adapter 12 V / 3 A	Adapter for fast battery charging.	•																
	A 1567	4400mAh battery pack	Li-Ion Battery pack 7,2V 4400mAh.	•																
	A 1568	8800mAh battery pack	Li-Ion Battery pack 7,2V 8800mAh.	•																

• Option