

> 800/4 Z Bits



Anwendung:


































Schlitzschrauben

Antrieb:

1/4"-Sechskant, passend für Halter nach
DIN 3126-F 6,3, ISO 1173

Ausführung:

Zähhart, besonders geeignet für den harten
Schraubfall z. B. in Blech oder Metall

							
Code	mm	mm	mm	mm	mm		
05059305001	0,5	3,0	50	2"	3,0	10	
05059466001	0,5	3,0	70	2 3/4"	3,0	10	
05059307001	0,5	4,0	50	2"	4,0	10	
05059310001	0,6	3,5	50	2"	3,5	10	
05059472001	0,6	3,5	70	2 3/4"	3,5	10	
05059450001	0,6	3,5	152	6"	3,5	10	
05059315001	0,6	4,5	50	2"	4,5	10	
05059489001	0,6	4,5	89	3 1/2"	4,5	10	
05059320001	0,8	4,0	50	2"	4,0	10	
05059478001	0,8	4,0	70	2 3/4"	4,0	10	
05059480001	0,8	4,0	89	3 1/2"	4,0	10	
05059451001	0,8	4,0	152	6"	4,0	10	
05059325001	0,8	5,5	50	2"	5,5	10	
05059330001	1,0	5,5	50	2"	5,5	10	
05059486001	1,0	5,5	70	2 3/4"	5,5	10	
05059488001	1,0	5,5	89	3 1/2"	5,5	10	
05059452001	1,0	5,5	152	6"	5,5	10	
05059335001	1,0	6,0	50	2"	6,0	10	
05059337001	1,2	6,5	50	2"	6,2	10	
05059492001	1,2	6,5	70	2 3/4"	6,2	10	
05059490001	1,2	6,5	89	3 1/2"	6,2	10	
05059453001	1,2	6,5	152	6"	6,2	10	
05059340001	1,2	8,0	50	2"	8,0	10	
05059496001	1,2	8,0	89	3 1/2"	8,0	10	
05059345001	1,6	8,0	50	2"	8,0	10	
05059500001	1,6	8,0	89	3 1/2"	8,0	10	