


REV.	DATE	DESCRIPTION
A	03/27/05	UPDATE DRAWING FORMAT

STAKE IN 4 PLACES
EQUALLY SPACED 90° APART
(INTERNAL)

1/4-36UNS-2B



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex		
7						DRAWN	G.R.S.			
6					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	CHECKED		PART DESCRIPTION SMA PLUG TO MMCX PLUG ADAPTER		
5						ISSUED				
4	RETAINER RING	BER. COPPER	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .316 - 1.180 = ± 0.016" 1.180 - 4.724 = ± 0.020"	SHEET	1 OF 1	PART NO. 242142		
3	CONTACT PIN	BRASS	GOLD	1						
2	INSULATOR	TEFLON	NATURAL	1	DD NOT SCALE DRAWING	CAD FILE		DWG. NO. 242142.DWG		
1	BODY	BRASS	GOLD	1		C:/242/242142.DWG				
	DESCRIPTION	MATERIAL	FINISH	QTY						