



- Material: PA 6.6 / Material: PA 6.6
- Entflammbarkeit : V2 (UL94) / UL Flammability: V2 (UL94)
- Temperaturbereich / Working temperature: -35°C ~ +85°C

- Alle Maße sind in mm. / All dimensions are in mm.
- Farbe: Natur / Color: Natural

ARTIKEL P/N	A	B	Bohrung Hole	Stärke Thickness	Bohrung Hole	Stärke Thickness	Stckz./ pcs.
8272 AA00	4.8	9.8	3.2	0.8 - 2.0	3.2	0.8 - 2.0	1.000
8273 AA00	6.4	11.4	3.2	0.8 - 2.0	3.2	0.8 - 2.0	1.000
8274 AA00	7.9	12.9	3.2	0.8 - 2.0	3.2	0.8 - 2.0	1.000
8275 AA00	9.5	14.5	3.2	0.8 - 2.0	3.2	0.8 - 2.0	1.000
8276 AA00	11.1	16.2	3.2	0.8 - 2.0	3.2	0.8 - 2.0	1.000
8277 AA00	12.7	17.7	3.2	0.8 - 2.0	3.2	0.8 - 2.0	1.000
8278 AA00	14.3	19.3	3.2	0.8 - 2.0	3.2	0.8 - 2.0	1.000
8279 AA00	15.9	20.9	3.2	0.8 - 2.0	3.2	0.8 - 2.0	1.000