



HAR-FLEX 12 POLE FEMALE CONNECTOR

HAR-FLEX 12 POLE FEMALE CONNECTOR

WIRING TABLE

C1	WIRE	C2
1	AWG 30	1
2	AWG 30	2
3	AWG 30	3
...
11	AWG 30	11
12	AWG 30	12

HARTING P/N	CABLE LENGTH (L)
33152430100374	100 ± 3
33152430200374	200 ± 5
33152430500374	500 ± 5

NOTES:

- 1.)CABLE MUST BE PERFORMED 100% CONTINUITE TEST AND HI-POT TEST.
- 2.)CABLE OPERATION TEMPERATURE: -20°C TO +105°C
- 3.)CABLE SHOULD BE PACKED BY THE PLASTIC BAG, THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION) EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY.
- 4.)WHITE LABEL CONTENT:

DATA CODE
HARTING P/N

	All rights reserved	Created by LINI Lin	Inspected by QINL Qin	Standardisation QINL Qin	Date 2021-03-10	State Final Release
	Department HCS - CN	Title Har-Flex 12Pole, Dul-end, W/O SR, L=xxMM			Doc-Key / ECM-Nr. 10083374/UGD/000/A 500000156050	
HARTING Customised Solutions D-32339 Espelkamp		Type TB	Number 33 15 243 XXX0374		Rev. A	Page 1/1