



**PCT-0300-050-RD-100**

E1517987

Cable Tie, 286x4.8mm, Red Plastic Barb

Cable ties in high industrial quality with rounded edges to prevent cable damage. Inclined tip to indicate usage direction and quick installation time. Material: Polyamid 6.6 Temp range: -40 degrees Celsius to +85 degrees Celsius Flammability rating: UL94-V2



## **Product Properties:**

<b>Model</b>	Internal toothing
<b>Material quality</b>	Polyamide (PA)
<b>Band closure</b>	Plastic lip/-cam
<b>UV-stable acc. ASTM D6779</b>	No
<b>Transparent</b>	No
<b>Solvable fastener</b>	No
<b>Text strip</b>	None
<b>Type of fastening</b>	None
<b>Colour</b>	Red
<b>Surface protection</b>	Untreated
<b>Material</b>	Plastic
<b>Halogen free</b>	Yes
<b>Operating temperature</b>	-40-85 °C
<b>Max. tensile force</b>	220 N

## **Dimensions:**

<b>Unit</b>	pcs
<b>Length belt/tape/tie</b>	286 mm

<b>Band width</b>	4.8 mm
<b>Max. bundle diameter</b>	81 mm
<b>Max. tensile force</b>	220 N
<b>MOQ</b>	100 .

### **Approvals:**

<b>Approved according to CE</b>	Yes
<b>Approved according to UR</b>	Yes
<b>With approval according to UL</b>	Yes
<b>Inflammability class of insulation material according to with UL94</b>	V2

### **Environmental information:**

<b>RoHS 3 (2015/863)</b>	Yes
<b>Conflict minerals</b>	N/A, Contains no conflict minerals
<b>Reach</b>	No SVHC (219 Subs. Jul 2021)

### **Logistic information:**

<b>Barcode</b>	733117640114
<b>E-no</b>	E1517987
<b>Country of origin</b>	TW
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>Stock code</b>	PCT-0300-050-RD-100
<b>Taric code</b>	39269097
<b>Unit</b>	pcs
<b>MOQ</b>	100 .