


## FF90319

O-Ring  
CAT FlangeO-Ring  
CAT FlanschJoint torique  
CAT Bride CoudeO-ring  
CAT FlangiaAnillo en O  
CAT Bride acodado

| Part<br>Number | Flange | D    | S   |
|----------------|--------|------|-----|
|                | Size   | mm   | mm  |
| FF90319-12     | -12    | 25,4 | 5,1 |
| FF90319-16     | -16    | 31,8 | 5,1 |
| FF90319-20     | -20    | 38,1 | 5,1 |
| FF90319-24     | -24    | 44,7 | 5,1 |
| FF90319-32     | -32    | 64,0 | 5,1 |

°C = -40 °C - +100 °C  
Material: NITRILE (Buna-N)


°C = -40 °C - +100 °C  
Material: NITRILE (Buna-N)

°C = -40 °C - +100 °C  
Material: NITRILE (Buna-N)

°C = -40 °C - +100 °C  
Material: NITRILE (Buna-N)

°C = -40 °C - +100 °C  
Material: NITRILE (Buna-N)

## 05.071

O-Ring  
GH466-32O-Ring  
GH466-32Joint torique  
GH466-32O-Ring  
GH466-32Anillo en O  
GH466-32

| Part<br>Number    | Flange | D     | S    |
|-------------------|--------|-------|------|
|                   | Size   | mm    | mm   |
| 05.071-44.12x2.62 | -32    | 44,12 | 2,62 |

\* Size -32 (ND 51) needs 2  
O-rings per nipple:  
05.071-44.12x2.62 -> O-rings  
must be ordered  
separately.

\* Größe -32 (DN51) benötigt  
2 O-Ringe pro Nippel: Nr.  
05.071-44.12x2.62 ->  
O-Ringe müssen sep.  
bestellt werden.

\* Module-32 (ND 51)  
nécessite 2 joints torique  
par embout:  
05.071-44.12x2.62 -> Les  
joints doivent être  
cocommander séparément.

\* La gradezza -32 (ND 51)  
necessita di 2 O-rings per  
nipplo: 05.071-44.12x2.62 ->  
O-rings devono essere  
ordinati separatamente.

\* La medida 32 (ND 51)  
necesita 2 juntas por racor:  
05.071-44.12x2.62 -> Las  
juntas deben solicitarse por  
separado.