

# Adapter Box for RS-232 Connection

## A232

Part Number



### Technical Data

#### Electrical Data

Supply Voltage	10...30 V DC
Current Consumption (U <sub>b</sub> = 24 V)	< 20 mA
Reverse Polarity Protection	yes
Interface	RS-232

#### Mechanical Data

Degree of Protection	IP65
Temperature Range	-25...60 °C
Housing Material	Plastic
Scope of delivery	Connection Cable
Packaging unit	1 Piece

Suitable Connection Equipment No.

**2**

- Connection cable SUB D, 9-pin included in delivery

