

## Product information

# 97 52 63 DG

## Four-Mandrel Crimping Pliers for turned contacts




- Crimping capacity can be adjusted in increments of 0.01 mm
- With digital display of the preset crimping capacities and possibility of re-calibration via RESET function with electronic wear monitoring
- Adjustment in mm, inches or comparable selection positions according to MIL
- Pliers in a plastic case with foam insert and standard locator for precise positioning of the contacts
- For crimping turned contacts
- Four-mandrel crimping for top-quality crimping connections
- Mandrel gauge to check the basic setting
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- High operation comfort thanks to handy shape
- Chrome vanadium electric steel in special quality, oil-hardened

### General

Article No.	97 52 63 DG
EAN	4003773063209
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	388 g
Dimensions	195 x 82 x 19 mm
Reach	yes
RohS	no

### Technical details



Applications	turned contacts
Capacity in square millimetres	0.08 — 2.5 mm <sup>2</sup>
AWG	28 — 14
Number of crimping positions	1
Max. contact diameter	5 mm

### Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

*technical change and errors excepted*



Standard locator