



Main

Range of product	Altivar
Product or component type	Communication module

Complementary

Range compatibility	Altivar Machine ATV320 Altivar 32 Lexium 32
Product compatibility	Lexium 32
Communication port protocol	Modbus TCP Ethernet/IP
Electrical connection	1 connector RJ45, Ethernet/IP 1 connector RJ45, Modbus TCP
Transmission rate	10/100 Mbps
Addressing	IP addressing manual, BOOTP or DHCP
Exchange mode	Half duplex and full duplex
Communication service	Up to 8 connections (includes connections of Modbus TCP/Ethernet IP) Ethernet IP/Modbus TCP FDR Agent Ethernet IP/Modbus TCP Read holding registers (03), 63 words max Modbus TCP Read input registers (04), 63 words max Modbus TCP Write single register (06) Modbus TCP Write multiple registers (16), 63 words max Modbus TCP Read/Write multiple registers (23) Modbus TCP Read device identification (43) Modbus TCP Diagnostics (08) Modbus TCP I/O scanner : read/write, 6 words maximum Modbus TCP Communication monitoring Modbus TCP SNMP agent Ethernet IP Master/Slave hierarchy ODVA AC drive profile and CiA 402 profile Ethernet IP Fixed communication monitoring adjusted by Ethernet IP scanner adaptor (Master) Ethernet IP
Display type	1 LED MS (Module Status) 1 LED NS (Network Status) 1 LED Ethernet port activity 1 LED Modbus TCP port activity
Net Weight	0.66 lb(US) (0.3 kg)

Ordering and shipping details

Category	18263 - LEXIUM 32 ACCESSORIES
Discount Schedule	PC51
GTIN	00785901924975
Nbr. of units in pkg.	1
Package weight(Lbs)	0.13 lb(US) (0.06 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.65 in (4.2 cm)
Package 1 width	2.40 in (6.1 cm)
Package 1 Length	3.54 in (9 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------