


## **Model 3844 Adapter TNC Male To BNC Female**



## **MATERIALS:**

Body – Brass, Tarnish Resistant Plating, Center Contact, Male: Gold Plated Brass, Female: Gold Plated Beryllium

Copper

Dielectric: Teflon

Marking: "Pomona 3844"

## **RATING:**

Operating Voltage: Shield/Earth 30VAC/60WVDC Max.

Inner Conductor/Shield: 500VRMS. Max.

Nominal Impedance: 50 Ohms

**ORDERING INFORMATION:** Model 3844

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

> Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060