

Multi-function tool HSS 90°

For universal use up to 1300 N/mm²

ORION[®]

Application:

For centring, drilling, countersinking, chamfering and peripheral milling.

Execution:

- Spiral-fluted design with grinding relief

Advantage:

- Universal point geometry ensures a broad range of uses
- TiNAlOX coating for increased service life requirements



Art. no.	11022 050
Brand	ORION
Manufacturer Part Number	11022050
Angle of the tip	90 Degree
Cutting material	HSS
Surface	TiNAlOX
Tool holding device	HA parallel shank
Cutting edge diameter	5 mm
Shank diameter	5 mm
Cutting edge length	10 mm
Length	60 mm
f steel 700	0.05 mm/r
Gross Weight	0.009 kg
Product Group	1AO

EAN

4039247793150