

## Studs



### Version:

- Tempered
- Rolled thread
- M 6 to M12 tempered to strength class 10.9
- M14 to M42 tempered to strength class 8.8.



<b>Art. no.</b>	<b>26197 100</b>
<b>Thread dimension</b>	M10
<b>Thread length</b>	13 mm
<b>Thread length 2 (metric thread)</b>	25 mm
<b>Length</b>	50 mm
<b>DIN</b>	6379

### EAN-Code

4020772081294