

## Electronic 3-point internal micrometer set

Micromar 44 EWR



### Application:

For measuring through-bores and for blind holes and short centring shoulders.

### Version:

- Self-centring and self-aligning
- Carbide-tipped measuring faces
- Interchangeable measuring heads
- Locking function
- Zero setting at any position
- mm/inch changeover
- ABS function
- preset function
- from Ø 40 mm, aluminium measuring head
- incl. setting rings

### Delivery:

1 measuring element, measuring heads with setting rings, battery (1 x 3 V lithium type CR 2032)



<b>Art. no.</b>	<b>31912 540</b>
<b>Min./max. length measuring range</b>	50-100 mm
<b>Measuring depth</b>	79/97 mm
<b>Error limit</b>	5 µm
<b>Data transmission type</b>	multiCOM
<b>Digit increment</b>	0.001 mm
<b>IP protection class</b>	IP 52
<b>Calibration Group</b>	I
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	3V CR2032 Lithium
<b>DIN</b>	863

### EAN-Code

4059192011031