

ESD shelf trolley with three load areas, load capacity 250 kg

Load area 410 x 610 and 820 x 610 mm

fetra
Transportgeräte

Application:

For the storage, serving and transportation of goods and materials in Euro crates.

Execution:

- Steel tube/profile steel welded
- with 3 electrically conductive wooden plates,
- edge 7 mm high
- Shelf frames, variable screw-in design, grid
- 50 mm
- Angle for tilted installation at 15° and 30°

Delivery:

Disassembled



Art. no.	50268 734
Brand	FETRA
Manufacturer Part Number	9391
Load-carrying capacity	250 kg
ESD-capable	Yes
Colour	Slate grey RAL 7015
Number of loading surfaces	3
Loading surface size	820 x 610 mm
Loading surface length	820 mm
Loading-surface width	610 mm
Length	935 mm
Width	666 mm
Height	1101 mm
Length x width x height	935 x 666 x 1101 mm
Loading-surface height	264 mm
Loading-surface height 2	564 mm
Loading-surface height 3	864 mm
With wheel lock	Yes
Wheel diameter	125 mm
Material of wheel	TPE-ESD
Wheel width	32 mm
Total stop optional	No
Number of steering rollers	4
Gross Weight	54.700 kg
Product Group	5AB

EAN

4017976493916