

Pneumatic straight grinder G 352 D

**MANNESMANN
DEMAG**

Application:

For light deburring work

Delivery:

Includes hose unit and collet chuck keys



Art. no.	75061 065
Brand	MANNESMANN DEMAG
Manufacturer Part Number	29946065
Model	G 352 D
Valve design	Rotary valve
Max. idle speed	35000 rpm
Min./max. idle speed	0-35000 rpm
Power output	290 W
Air consumption	7.5 l/s
Connection thread	G 1/4 inch
Sound-pressure level	73 dB
Length	171 mm
Diameter of housing	30 mm
Collet chuck diameter	6 mm
Suitable for max. sanding block diameter	16 mm
Max. HM rotating milling cutter diameter	10 mm
Weight	0.36 kg
Gross Weight	1.320 kg
Product Group	7AA

EAN

4251757300493