

Column-mounted slewing jib crane ASSISTENT AS – complete set with chain hoist

Lives up to its name



Application:

Perfect for halls/rooms with low ceilings.

Execution:


- classification according to EN 13001 HC2 S2 HD2 for light industrial use
- power supply with round trailing cable
- lockable isolating switch
- Operating voltage: 400 V/50 Hz, control voltage: 24 V
- Electric chain hoist with manual sliding chassis – two-stage lifting speed
- Swivel range 180°

Advantage:

- Solid construction
- Ideal for halls/rooms with low ceilings

Delivery:

Incl. detailed documentation



Art. no.	77110 031
Brand	VETTER
Manufacturer Part Number	AW10-4,0+SIXX6F-HF
Model	ASSISTENT AW
Type	Console assembly B
Load-carrying capacity	1000 kg
Overhang	4000 mm
Max. lift height	5 m
Design	With electric chain hoist
Lifting device design	With electric chain hoist SiXX-HF
Flange width	150 mm
Swivel range	180 Degree
Colour	Daffodil yellow RAL 1007
Surface	Lacquered
Operating voltage	400 V
Cable length	3.8 m
Weight	334 kg
Max. vertical force	13 kN
Max. horizontal force	41 kN
Gross Weight	416.000 kg
Product Group	7EL